



Drop-in/Under-mount Bathroom Sink 111-0

Features

- Center drain, no overflow.

Material

- Premium 20-gauge stainless steel with luster finish.

Installation

- Drop-in or undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner







Codes/Standards

None Applicable

STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

- Installation: Drop-in, Under-mount
- Bowl area (Only): Length: 8-7/8" (225 mm)
Width: 8-7/8" (225 mm)
Bowl depth: 4" (102 mm)
- Drain hole: 2" (51 mm)
- Template: 1033101-7, not required, not included

Notes

Install this product according to the installation instructions.