



Drop-in/undermount bathroom sink 111-0

Features

- No faucet holes; requires wall- or counter-mount faucet.
- Center drain, no overflow.

Material

- Premium 20-gauge stainless steel with luster finish.

Installation

- Drop-in or undermount.

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner







Codes/Standards

None Applicable

STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Installation:	Drop-in, Under-mount
Bowl area (Only):	Length: 8-7/8" (225 mm)
	Width: 8-7/8" (225 mm)
	Bowl depth: 4" (102 mm)
Drain hole:	2" (51 mm)
Template:	1033101-7, not required, not included

Notes

Install this product according to the installation instructions.