

WINDHAM_{TM}

Features


- · Vitreous china
- Sterling Pro Force® HET Flushing Technology
- 5-year limited warranty
- Flushes efficiently regardless of incoming water pressure
- Three-bolt, quick-connect installation system
- Standard round or elongated seat not supplied
- 1.28 gpf (4.8 lpf)
- One flush cleansing performance
- 12" (305 mm) rough-in
- Large 8" (203 mm) x 9" (229 mm) water surface and full 2" (51 mm) fully glazed trapway
- 27-1/4" (692 mm) x 16-7/8" (429 mm) x 29" (737 mm) [402080]
- 29-1/4" (743 mm) x 16-7/8" (429 mm) x 29" (737 mm) [402081]

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- EPA WaterSense®

HET-HIGH EFFICIENCY TOILET 402080 ALSO 402081



Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Included Tank	Included Bowl	Colors/Finish	es
402080	HET-High Efficiency Toilet, with round-front bowl	404555	403015	□ 0	□ Other
402081	HET-High Efficiency Toilet, with elongated bowl	404555	403215	0	□ Other

WINDHAM


Technical Information

Fixture:			
Configuration	2-piece		
Water per full flush	1.28 gal (4.8 L)		
Passageway	2" (51 mm)		
Water area	8" (203 mm) x 9" (229 mm)		
Seat post hole centers	5-1/2" (140 mm)		

Included components:		
Tank lid	84537	
Trip lever	84625	
Bolt cap accessory pack	1013092	

Installation Notes

One flush cleansing of the bowl per ASME A112.19.2/CSA B45.1 and Dual Force® toilets per ASME A112.19.14-2006 performance requirements, when installed and operated per instructions packed with the product.



Product Diagram

