



# Southaven®

Top-mount Kitchen Sink  
**11402-3**

## Features

- Three faucet holes.
- 8" (203 mm) depth.
- 3-5/8" (92 mm) drain opening.
- Satin finish.

## Material

- Premium 20-gauge stainless steel.

## Installation

- Top-mount.

## Recommended Products/Accessories

7400 Sink Strainer  
11861 Sink Rack  
K-6139 Sponge Caddy  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

## Included Components

Product consists of:  
1150001 Installation Clips




## Codes/Standards

ASME A112.19.3/CSA B45.4

## STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Installation: Top-mount

Cutout: Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1/2" (13 mm) radius corners

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14" (356 mm)  
Width: 15-1/8" (384 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Bowl area (Right): Length: 14" (356 mm)  
Width: 15-1/8" (384 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Number of deck holes: 3

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1032929-7, not required, not included

### Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.