



# Southhaven®

33" top-mount double-bowl kitchen sink

## 11402-4

### Features

- Four faucet holes
- 8" (203 mm) depth
- 3-5/8" (92 mm) drain opening
- Satin finish

### Material

- Premium 20-gauge stainless steel

### Installation

- Top-mount

### Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer  
11861 Sink Rack  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

### Included Components

1150001 Installation Clips




### Codes/Standards

ASME A112.19.3/CSA B45.4  
IAPMO Certification

### STERLING® Stainless Steel Sinks

#### Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Cutout: Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1/2" (13 mm) radius corners

Center(s): 4

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14" (356 mm)  
Width: 15-1/8" (384 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Bowl area (Right): Length: 14" (356 mm)  
Width: 15-1/8" (384 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Number of deck holes: 4

Faucet hole spacing: 4" (102 mm)

Faucet hole(s): 1-7/16" (37 mm)

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

3-24-2024 20:48 - US

### Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.