



**McAllister®**

31-3/4" undermount double-bowl kitchen sink  
**11409-L**

**Features**

- No faucet holes; requires wall- or counter-mount faucet
- 8-5/16" (203 mm) depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish

**Material**

- Premium 18-gauge stainless steel

**Installation**

- Undermount

**Recommended Products/Accessories**

- 7400 Stainless Steel Sink Drain and Strainer
- 11862 Sink Rack
- 11863 Sink Rack
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

**Included Components**

- 91915 Hardware Kit




**Codes/Standards**

ASME A112.19.3/CSA B45.4  
IAPMO Certification


**STERLING® Stainless Steel Sinks  
Lifetime Limited Warranty**

See website for detailed warranty information.



Mounting bracket assembly provides a secure installation.



Reveal



No Reveal



**Technical Information**

All product dimensions are nominal.

- Bowl configuration: Off-set Large/small
- Bowl area (Left): Length: 14-1/4" (362 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)
- Bowl area (Right): Length: 14-1/4" (362 mm)  
Width: 18-1/2" (470 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)
- Drain hole: 3-3/4" (95 mm)
- Template: 1315848-7, required, included

**Notes**

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.
- Use the supplied cut-out template to select either a hidden or exposed rim.