

# Features

- 8-5/16"-deep double bowls.
- 3-3/4" drain opening.
- Stainless steel with luster finish.
- SilentShield<sup>®</sup> sound-absorption technology offers quieter performance.

# Material

• Premium 18-gauge stainless steel.

# Installation


- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

# **Recommended Products/Accessories**

7400 Sink Strainer 11862 Sink Rack 11863 Sink Rack K-6139 Sponge Caddy K-23726 Drain treatment K-23729 Stainless steel cleaner

## **Included Components**

Product consists of: 91915 Hardware Kit



**McAllister**®


**Under-Mount Kitchen Sink** 

#### Codes/Standards ASME A112.19.3/CSA B45.4

# STERLING<sup>®</sup> Warranty - Stainless Steel Sinks


See website for detailed warranty information.






# McAllister® Under-Mount Kitchen Sink 11409

Mounting bracket assembly provides a secure installation.





# **Technical Information**

All product dimensions	s are nominal.
Bowl configuration:	Off-set Large/small
Installation:	Under-mount
Bowl area (Left):	Length: 14-1/4" (362 mm)
	Width: 18-1/2" (470 mm)
	Bowl depth: 8" (203 mm)
	Water depth: 8" (203 mm)
Bowl area (Right):	Length: 14-1/4" (362 mm)
	Width: 15-3/4" (400 mm)
	Bowl depth: 8" (203 mm)
	Water depth: 8" (203 mm)
Drain hole:	3-3/4" (95 mm)
Template:	1315847-7, required, included

## Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Use the supplied cut-out template to select either a hidden or exposed rim.