



Carthage® Under-Mount Kitchen Sink 11445

Features

- No faucet holes; requires wall- or counter-mount faucet.
- 8-9/16" (217 mm) depth.
- 3-5/8" (92 mm) drain opening.
- Stainless steel with luster finish.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.

Recommended Products/Accessories

- 7400 Sink Strainer
- 11861 Sink Rack
- K-6139 Sponge Caddy
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- Product consists of:
- 91915 Hardware Kit



Codes/Standards

ASME A112.19.3/CSA B45.4

STERLING® Warranty - Stainless Steel Sinks


See website for detailed warranty information.

DISCONTINUED This product has been discontinued.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.



Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Installation: Under-mount

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14-1/16" (357 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 8-9/16" (218 mm)
Water depth: 8-1/16" (205 mm)

Bowl area (Right): Length: 14-1/16" (357 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 8-9/16" (218 mm)
Water depth: 8-9/16" (218 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1315846-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Use the supplied cut-out template to select either a hidden or exposed rim.