

Features

- 8"-deep single bowl.
- 3-3/4" drain opening.
- Stainless steel with luster finish.
- SilentShield[®] sound-absorption technology offers quieter performance.
- Rectangular bowl.
- Includes reveal and no-reveal option.
- Single pack.
- Strainer not included.

Material

Premium 20-gauge stainless steel.

Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

7400 Sink Strainer K-23726 Drain treatment K-23729 Stainless steel cleaner

Included Components

Additional Components: 91915 Hardware Kit



McAllister®

11447

under-mount kitchen sink

Codes/Standards

ASME A112.19.3/CSA B45.4


STERLING[®] Warranty - Stainless Steel Sinks See website for detailed warranty information.

McAllister®

under-mount kitchen sink

11447

Mounting bracket assembly provides a secure installation.



Technical Information

STERLIN

A KOHLER, COMPANY

All product dimensions are nominal.	
Bowl configuration:	Single
Installation:	Under-mount
Min. base cabinet width:	27" (686 mm)
Bowl area (Only):	Length: 20-7/8" (530 mm) Width: 15-7/16" (392 mm) Bowl depth: 8" (203 mm) Water depth: 7-3/4" (197 mm)
Drain hole: Template:	3-1/2" (89 mm) 1315840-7, required, included

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.