



Springdale®

16-1/4" undermount single-bowl bar sink

11448

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8" (203 mm) depth
- 3-3/4" (95 mm) drain opening
- Stainless steel with luster finish
- Rectangular bowl
- No faucet holes; requires wall- or counter-mount faucet
- Luster finish
- 11448 = single pack
- J11448 = 3 per pack
- T11448 = 20 per pack
- 16-1/4" (413 mm) x 17-3/4" (451 mm) x 8" (203 mm)
- Sink drain with strainer sold separately

Material

- Premium 18-gauge stainless steel

Installation

- Undermount
- Can be installed with or without reveal

Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer
11862 Sink Rack
K-23726 Drain treatment
K-23729 Stainless steel cleaner

Included Components

91915 Hardware Kit



ADA

Codes/Standards

ASME A112.19.3/CSA B45.4
ADA
ICC/ANSI A117.1
IAPMO Certification

STERLING® Stainless Steel Sinks Lifetime Limited Warranty


See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)



Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-25-2024 21:05 - US



Mounting bracket assembly provides a secure installation.



Technical Information

All product dimensions are nominal.

- Bowl configuration: Single
- Min. base cabinet width: 21" (533 mm)
- Bowl area (Only): Length: 14-1/4" (362 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 8" (203 mm)
Water depth: 8" (203 mm)
- Drain hole: 3-3/4" (95 mm)
- Template: 1315843-7, required, included

Notes

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.
- Use the supplied cut-out template to select either a hidden or exposed rim.
- ADA compliant when installed to the specific requirements of these regulations.
- ADA permits a parallel approach to wet bars.