



# Cinch®

## Under-Mount Kitchen Sink

### 11722

#### Features

- 9-5/16"-deep single bowl.
- 3-5/8" rear drain opening.
- Stainless steel with luster finish.
- SilentShield® sound-absorption technology offers quieter performance.

#### Material

- Premium 18-gauge stainless steel.

#### Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

#### Recommended Products/Accessories

7400 Sink Strainer  
15287 Sink Rack  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

#### Included Components

Product consists of:  
91915 Hardware Kit




#### Codes/Standards

ASME A112.19.3/CSA B45.4

#### STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Under-mount

Min. base cabinet width: 30" (762 mm)

Bowl area (Only): Length: 24-1/2" (622 mm)  
Width: 14-7/8" (378 mm)  
Bowl depth: 9-5/16" (237 mm)  
Water depth: 9-5/16" (237 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1105665-7, required, included

### Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.