



# Southaven®

33" top-mount double-bowl kitchen sink  
**11850-3**

### Features

- Three faucet holes
- 8-1/2" (217 mm) depth
- 3-5/8" (92 mm) drain opening
- Satin finish

### Material

- Premium 18-gauge stainless steel

### Installation

- Top-mount

### Recommended Products/Accessories

- 7400 Stainless Steel Sink Drain and Strainer
- 11861 Sink Rack
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

### Included Components

- 1150001 Installation Clips




### Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

### STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

- Bowl configuration: Double equal
- Cutout: Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1/2" (13 mm) radius corners
- Min. base cabinet width: 36" (914 mm)
- Bowl area (Left): Length: 14" (356 mm)  
Width: 15-1/8" (384 mm)  
Bowl depth: 8-1/2" (216 mm)  
Water depth: 8-1/2" (216 mm)
- Bowl area (Right): Length: 14" (356 mm)  
Width: 15-1/8" (384 mm)  
Bowl depth: 8-1/2" (216 mm)  
Water depth: 8-1/2" (216 mm)
- Number of deck holes: 3
- Faucet hole(s): 1-7/16" (37 mm)
- Drain hole: 3-5/8" (92 mm)

**Notes**

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.