

1296162-SHP (1200 mm Right)
1296163-SHP (1200 mm Left)
1296164-SHP (1500 mm Right)
1296165-SHP (1500 mm Left)

1296172-SHP (48")
1296173-SHP (60")

1296210-CP

1296212

4.1795.189

4.1795.146

1296210-CP

1296171-CP

1296209

1292318-SHP

1292321-SHP (Left)
1292322-SHP (Right)

Included with 1296209

1298943-SHP (48" Left)
1298944-SHP (48" Right)
1298945-SHP (60" Left)
1298946-SHP (60" Right)

1292321-SHP (Left)
1292322-SHP (Right)

4.1795.146

1292318-SHP

1292350

1296166-SHP (48" Left)
1296167-SHP (48" Right)
1296168-SHP (60" Left)
1296169-SHP (60" Right)