



# Middleton®

## Top-mount Kitchen Sink

### 14633-4F

#### Features

- Four faucet holes.
- 6"-deep double bowls.
- 3-5/8" (92 mm) drain opening.
- Stainless steel with luster finish.
- SilentShield® sound-absorption technology offers quieter performance.

#### Material

- Premium 20-gauge stainless steel.

#### Installation

- Top-mount.

#### Recommended Products/Accessories

7400 Sink Strainer  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

#### Included Components

Product consists of:  
1150001 Installation Clips



ADA

#### Codes/Standards

ASME A112.19.3/CSA B45.4  
ADA  
ICC/ANSI A117.1

#### STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.




---

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

8-20-2020 16:14 - US



**Technical Information**

All product dimensions are nominal.

- Bowl configuration: Double equal
- Installation: Top-mount
- Cutout: Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 11/16" (18 mm) radius corners
- Bowl area (Left):
  - Length: 13-3/4" (349 mm)
  - Width: 15-1/2" (394 mm)
  - Bowl depth: 6" (152 mm)
  - Water depth: 6" (152 mm)
- Bowl area (Right):
  - Length: 13-3/4" (349 mm)
  - Width: 15-1/2" (394 mm)
  - Bowl depth: 6" (152 mm)
  - Water depth: 6" (152 mm)
- Number of deck holes: 4
- Faucet hole spacing: 4" (102 mm)
- Faucet hole(s): 1-7/16" (37 mm)
- Drain hole: 3-5/8" (92 mm)

**Notes**

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.
- ADA compliant when installed to the specific requirements of these regulations.