



**Middleton®**  
Top-mount Kitchen Sink  
**14711-4**

**Features**

- Four faucet holes.
- 8"-deep single bowl.
- 3-5/8" (92 mm) drain opening.
- Stainless steel with durable satin finish.
- SilentShield® sound-absorption technology offers quieter performance.

**Material**

- Premium 20-gauge stainless steel.

**Installation**

- Top-mount.

**Recommended Products/Accessories**

7400 Sink Strainer  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

**Included Components**

Product consists of:  
1150001 Installation Clips




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**STERLING® Warranty - Stainless Steel Sinks**

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

- Bowl configuration: Single
- Installation: Top-mount
- Cutout: Top-mount, 24-1/2" x 21-1/2" (622 mm x 546 mm) with 1/2" (13 mm) radius corners
- Bowl area (Only): Length: 21" (533 mm)  
Width: 15-1/4" (387 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)
- Number of deck holes: 4
- Faucet hole spacing: 4" (102 mm)
- Faucet hole(s): 1-7/16" (37 mm)
- Drain hole: 3-5/8" (92 mm)

**Notes**

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.