



Vista Pivot™ II

Framed pivot shower door
1500D-42

Features

- Framed, 1/8" (3 mm) thick tempered glass
- Tempered glass ensures enhanced safety and durability
- 13" (330 mm) inline panel, 5/32" (4 mm) thick

Material

- Anodized aluminum prevents rust and corrosion

Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality
- For residential use only



Codes/Standards


ANSI Z97.1
 CAN/CGSB-12.1
 CPSC 16CFR 1201

STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	S	Silver

Available Glass Options

Code	Description
	Pebbled



Technical Information

All product dimensions are nominal.

- Base-To-Wall 3/8" (10 mm)
- Radius – Max:
- Shower Ledge Min 1-1/8" (29 mm)
- Flat:
- Shower Wall Min 1-1/4" (32 mm)
- Flat:

Notes

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 67" (1702 mm) to allow for installation clearance.