



# Vista Pivot™ II

Framed pivot shower door

## 1505D-36

### Features

- Framed, 1/8" (3 mm) thick tempered glass
- Tempered glass ensures enhanced safety and durability
- 7" (178 mm) inline panel 5/32" (4 mm) thick

### Material

- Anodized aluminum prevents rust and corrosion

### Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality
- For residential use only

### Recommended Replacements

- This product is replaced by 707531-D3.



### Codes/Standards


ANSI Z97.1  
CAN/CGSB-12.1  
CPSC 16CFR 1201

### STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

### Available Glass Options

Code	Description
	Brownstone™
	Frosted
	Pebbled
	Rain
	Tangle™



### Technical Information

All product dimensions are nominal.

Base-To-Wall	3/8" (10 mm)
Radius – Max:	
Shower Ledge Min	1-1/8" (29 mm)
Flat:	
Shower Wall Min	1-1/4" (32 mm)
Flat:	

### Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 67" (1702 mm) to allow for installation clearance.