



Vista Pivot™ II

Framed pivot shower door

1507D-31

Features

- 5" In-line panel consists of clear glass for clear and patterned glass options; textured glass options will have matching panel
- Full-length magnetic door latch
- Maximum 3-1/2" width adjustability w/ in-line panel
- Tempered glass ensures enhanced safety and durability

Installation

- Door can be installed to open to the left or right to suit your bathroom layout
- Door can be installed to open to the left or right to suit your bathroom layout
- Not for use in hospitality
- For residential use only

Recommended Replacements

- This product is replaced by 707510-D3.



Codes/Standards

ANSI Z97.1
CAN/CGSB-12.1
CPSC 16CFR 1201



STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

Available Glass Options

Code	Description
------	-------------

	Ellipse
--	---------



Technical Information

All product dimensions are nominal.

Base-To-Wall	3/8" (10 mm)
Radius – Max:	
Shower Ledge Min	1-1/8" (29 mm)
Flat:	
Shower Wall Min	1-1/4" (32 mm)
Flat:	

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 67" (1702 mm) to allow for installation clearance.