



# Vista Pivot™ II

Framed pivot shower door  
1530D-42

## Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.
- 13" (330 mm) inline panel, 5/32" (4 mm) thick.

## Installation

- Not for use in hospitality.
- For residential use only.

## Recommended Products/Accessories

K-23723 Faucet cleaner

## Included Components

Additional Components:  
Hardware kit



## Codes/Standards

ANSI Z97.1  
CPSC 16CFR 1201


## STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*


Color	Code	Description
-------	------	-------------

	S	Silver
--	---	--------

## Available Glass Options

Code	Description
------	-------------

	Pebbled
--	---------



**Technical Information**

All product dimensions are nominal.  
 Installation type: For shower base installation  
 Opening Width - Min: 36" (914 mm)  
 Opening Width - Max: 42" (1067 mm)  
 Walk-through - Min: 18-15/16" (481 mm)  
 Walk-through - Max: 24-15/16" (633 mm)  
 Base-To-Wall Radius 3/8" (10 mm)  
 – Max:  
 Glass thickness: 1/8" (3 mm)

**Notes**

Install this product according to the installation guide.  
 The vertical opening should be a minimum of 70-1/2" (1791 mm) to allow for installation clearance.