



Vista Pivot™ II

Framed pivot shower door

1530D-42

Features

- Framed, 1/8" (3 mm) thick tempered glass
- Tempered glass ensures enhanced safety and durability
- 13" (330 mm) inline panel, 5/32" (4 mm) thick

Material

- Anodized aluminum prevents rust and corrosion

Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality
- For residential use only



Codes/Standards


ANSI Z97.1
CAN/CGSB-12.1
CPSC 16CFR 1201

STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

Available Glass Options

Code	Description
	Pebbled



Technical Information

All product dimensions are nominal.

Base-To-Wall	3/8" (10 mm)
Radius – Max:	
Shower Ledge Min	1-1/8" (29 mm)
Flat:	
Shower Wall Min	1-1/4" (32 mm)
Flat:	

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 70-1/2" (1791 mm) to allow for installation clearance.