

Ludington® Under-Mount Kitchen Sink 20022

Features

- 9-9/16"-deep single bowl.
- 3-3/4" drain opening.
- SilentShield® sound-absorption technology offers quieter performance.

Material

- Stainless steel with satin finish.
- Premium 18-gauge stainless steel.

Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

7400 Sink Strainer 20285 Silicone sink mat K-23726 Drain treatment K-23729 Stainless steel cleaner



Codes/Standards ASME A112.19.3/CSA B45.4


STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



Ludington®

Under-Mount Kitchen Sink 20022



Technical Information

All product dimensions are nominal.

Installation: Under-mount Min. base cabinet 36" (914 mm)

width:

Bowl area (Only): Length: 30-1/4" (768 mm)

Width: 16-9/16" (420 mm) Bowl depth: 9-5/16" (237 mm) Water depth: 9-5/16" (237 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1298947-7, required, included

Notes

Install this product according to the installation instructions.

Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-43-FOCUS). Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.