



Ludington®

34" undermount single-bowl farmhouse kitchen sink

20243-PC

Features

- Apron-front
- No faucet holes; requires wall- or counter-mount faucet
- 9-1/2" (241 mm) depth provides generous workspace
- 3-3/4" (94 mm) drain opening
- 36" minimum base cabinet width
- Includes silicone sink mat (20285-ASH) and sink drain and strainer (7400)

Material

- Stainless steel with satin finish
- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- 20285 Silicone sink mat
- 7400 Stainless Steel Sink Drain and Strainer




Codes/Standards

ASME A112.19.3/CSA B45.4
IAPMO Certification

STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Min. base cabinet width: 36" (914 mm)

Bowl area (Only): Length: 30-1/4" (768 mm)
Width: 16-9/16" (420 mm)
Bowl depth: 9-3/16" (233 mm)
Water depth: 9-3/16" (233 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1307774-7, required, included

Notes

Install this product according to the installation instructions.

Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-43-FOCUS). Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.