



McAllister®

Under-Mount Kitchen Sink

24765

Features

- 5-15/16"-deep double bowls.
- 3-3/4" drain opening.
- Stainless steel with luster finish.
- SilentShield® sound-absorption technology offers quieter performance.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

K-23726 Drain treatment
K-23729 Stainless steel cleaner

Optional Products/Accessories

11861 Sink Rack
7400 Sink Strainer



ADA

Codes/Standards

ASME A112.19.3/CSA B45.4
ADA
ICC/ANSI A117.1

STERLING® Warranty - Stainless Steel Sinks


See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-24-2020 06:18 - US



Technical Information

All product dimensions are nominal.

- Bowl configuration: Double equal
- Installation: Under-mount
- Bowl area (Left): Length: 14-1/8" (358 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 5-5/8" (143 mm)
Water depth: 5-5/8" (143 mm)
- Bowl area (Right): Length: 14-1/8" (358 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 5-5/8" (143 mm)
Water depth: 5-5/8" (143 mm)
- Drain hole: 3-5/8" (92 mm)
- Template: 1315846-7, required, included

Notes

- Install this product according to the installation instructions.
- ADA compliant when installed to the specific requirements of these regulations.