



McAllister®

Undermount double-equal kitchen sink

24765

Features

- No faucet holes; requires wall- or counter-mount faucet.
- 5-15/16" depth.
- 3-3/4" drain opening.
- Stainless steel with luster finish.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- 11861 Sink Rack
- 7400 Sink Strainer



ADA

Codes/Standards

- ASME A112.19.3/CSA B45.4
- ADA
- ICC/ANSI A117.1


STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.



Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Installation: Under-mount

Bowl area (Left): Length: 14-1/8" (358 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 5-5/8" (143 mm)
Water depth: 5-5/8" (143 mm)

Bowl area (Right): Length: 14-1/8" (358 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 5-5/8" (143 mm)
Water depth: 5-5/8" (143 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1315846-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.