



# Southaven®

Top-mount Kitchen Sink  
**24912-3**

## Features

- Top-mount.
- Three faucet holes.
- 8"-deep single bowl.
- 3-5/8" drain opening.
- Stainless steel with satin deck and luster bowl finish.
- SilentShield® sound-absorption technology offers quieter performance.

## Material

- Premium 20-gauge stainless steel.

## Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner

## Optional Products/Accessories

7400 Sink Strainer




## Codes/Standards

ASME A112.19.3/CSA B45.4

## STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

- Installation: Top-mount
- Bowl area (Only): Length: 29-3/16" (742 mm)  
Width: 15-1/16" (383 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)
- Number of deck holes: 3
- Faucet hole(s): 1-7/16" (37 mm)
- Drain hole: 3-5/8" (92 mm)

**Notes**

Install this product according to the installation instructions.