



# Meritor®

## 33" top-mount/undermount double-bowl kitchen sink

### 28197-1

#### Features

- 36" (914 mm) minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Rounded corners are easy to clean
- Angled edge allows for easy sweeping of food or water from countertop to bowl
- SilentShield® sound-absorption technology offers quieter performance
- Single faucet hole
- Box includes: Sink, installation hardware
- Optional K-6401 sink rack (sold separately)

#### Material

- Sink constructed from premium 18-gauge stainless steel

#### Installation

- Top-mount or undermount

#### Recommended Products/Accessories

K-23729 Stainless steel cleaner

#### Optional Products/Accessories

- K-8799 Sink drain and strainer basket
- K-8801 Sink drain and strainer with tailpiece
- K-11352 Disposal Flange with Stopper




#### Codes/Standards

ASME A112.19.3/CSA B45.4  
IAPMO Certification

#### STERLING® One-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14-1/8" (359 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 9" (229 mm)

Bowl area (Right): Length: 14-1/8" (359 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 9" (229 mm)

Number of deck holes: 1

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-3/4" (94 mm)

Template: Top-mount/Undermount, 1476435-7, required, included

### Notes

Install this product according to the installation instructions.