



Southhaven® All-In-One 33" top-mount double-bowl kitchen sink kit 30230-2PC

Features

- 8-1/2" (217 mm) depth
- Two faucet holes
- 3-5/8" (92 mm) drain opening
- Two-function pull-down sprayhead allows you to switch from aerated stream to powerful ring spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Box includes: Sink, assembled Vibrant Stainless pull-down faucet, soap/lotion dispenser, supply lines, drains and strainers, installation hardware

Material

- Premium 18-gauge stainless steel
- Durable material construction
- STERLING finishes resist corrosion and tarnishing

Installation

- Top-mount
- Flexible supply lines simplify installation

Recommended Products/Accessories

- 11861 Sink Rack
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- 1150001 Installation Clips
- 1259745-VS Vibrant Stainless pull-down kitchen faucet with soap/lotion dispenser
- 7400 Stainless Steel Sink Drain and Strainer (Qty 2)



Codes/Standards

ASME A112.18.1/CSA B125.1
ASME A112.19.3/CSA B45.4
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
IAPMO Certification

STERLING® Stainless Steel Sinks Lifetime Limited Warranty


See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-25-2024 20:53 - US



Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Min. base cabinet width: 36" (914 mm)

Bowl area (Left):
Length: 14" (356 mm)
Width: 15-1/8" (384 mm)
Bowl depth: 8-1/2" (216 mm)
Water depth: 8-1/2" (216 mm)

Bowl area (Right):
Length: 14" (356 mm)
Width: 15-1/8" (384 mm)
Bowl depth: 8-1/2" (216 mm)
Water depth: 8-1/2" (216 mm)

Number of deck holes: 2

Faucet hole(s): 2" (51 mm)

Soap/Lotion hole: 1-7/16" (37 mm)

Drain hole: 3-5/8" (92 mm)

Notes

Install this product according to the installation instructions.