

### Features

- Two-piece installation
- 14" rough-in
- Elongated bowl
- 1.28 gallons per flush
- Pro Force flushing technology
- Three-bolt quick-connect installation system
- Limited 5-year warranty

### Recommended Products/Accessories

K-4636 Cachet® Quiet-Close™ Elongated Toilet Seat  
K-5588 Purefresh® Elongated Toilet Seat  
K-4108 C3®-230 Elongated Cleansing Toilet Seat  
K-5420 Low-Profile Bolt Caps

### Included Components

Product consists of:

404544 Toilet Tank  
403215 Toilet Bowl

Additional Components:

Bolt caps (pair)  
Tank cover  
tank hardware accessory pack  
trip lever



### Codes/Standards



ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)


### STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	KOHLER Biscuit



**Technical Information**

All product dimensions are nominal.

- Toilet type: Two-piece, Floor-mount
- Waste Outlet: Floor
- Bowl shape: Round-front
- Flush type: Gravity siphon rim jet
- Trap passageway: 2" (51 mm)
- Water Consumption
  - Full: 1.28 gpf (4.8 lpf)
- Water surface size: 8" x 9" (203 mm x 229 mm)
- Rough-in: 14" (356 mm)
- Seat-mounting holes: 5-1/2" (140 mm)

**Notes**

Install this product according to the installation instructions.  
Measure your actual product for roughing-in details.