



Brella™ Comfort Height®

Two-piece elongated 1.28 gpf chair height toilet

402095

Features

- Two-piece toilet.
- Elongated bowl offers added room and comfort.
- Skirted trapway simplifies cleaning.
- 1.28 gpf (4.8 lpf).
- Standard left-hand Polished Chrome trip lever included.
- 2" (51 mm) fully-glazed trapway.
- Combination consists of the 402101 bowl and 402098 tank.
- Standard 12" (305 mm) rough-in only. Cannot be combined with K-5383, or K-5381 for use in 10" or 14" installations.

Material

- Vitreous china.

Technology

- Uses the force of gravity and a precision-engineered tank, bowl, and trapway to deliver virtually plug-free performance.

Installation

- Standard 12" (305 mm) rough-in.
- Patented ReadyLock™ installation system is a simple solution for skirted toilets that saves time, hassle and eliminates the need to drill into the floor for a standard 12" (305 mm) rough-in.
- Seat and supply line sold separately.

Recommended Products/Accessories

K-4008 Reveal® Quiet-Close™ Elongated Toilet Seat
K-7637 Angle Supply with Stop (single)
K-23726 Drain treatment


Included Components

Product consists of:

402098 Toilet tank
402101 Elongated toilet bowl

Additional Components:

ReadyLock™ installation system
Tank cover
Trip lever



ADA

CSA B651

OBC

Codes/Standards

DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

Available Colors/Finishes


Color tiles intended for reference only.

Color Code Description



0 White

Brella™ Comfort Height®
Two-piece elongated 1.28 gpf chair height toilet
402095



Technical Information

All product dimensions are nominal.

Toilet type:	Two-piece, Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Trap passageway:	2" (51 mm)
Water Consumption	
Full:	1.28 gpf (4.8 lpf)
Water surface size:	5-1/16" x 4-9/16" (129 mm x 115 mm)
Rim to water surface:	8-9/16" (217 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Fixture Supply Requirements

Min static pressure:	15 psi (103.4 kPa)
Max static pressure:	80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.

ADA compliance will require a seat 1-inch thick minimum.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

Accessibility standards may require controls to be located on the open side of the toilet.