

Features

- 1.28 gpf (4.8 lpf).
- Standard left-hand Polished Chrome trip lever included.
- Combines with the 402101 bowl to create a complete 402095 Brella two-piece toilet.

Material

- Vitreous china.

Technology

- Uses the force of gravity and a precision-engineered tank, bowl, and trapway to deliver virtually plug-free performance.


Installation

- Three-bolt installation.
- Supply line sold separately.

Included Components

Additional Components:

Tank Cover, Trip Lever and Hardware kit



Codes/Standards

ASME A112.19.2/CSA B45.1

STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



0	White
---	-------



Brella™
Toilet tank
402098

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Water Consumption

Full: 1.28 gpf (4.8 lpf)

Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)

Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.