

Features

- 1.28 gpf (4.8 lpf)
- Left-hand Polished Chrome trip lever
- Combines with the 402101 bowl to create a complete 402095 Brella two-piece toilet
- Uses the force of gravity and a precision-engineered tank, bowl, and trapway to deliver virtually plug-free performance

Installation

- Three-bolt quick-connect installation
- Supply line sold separately



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification

STERLING® Toilet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White



Brella™
Toilet tank
402098

No image available.

This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount

Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)

Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.