

Brella™ Comfort Height®
Elongated toilet bowl
402101

Features

- Elongated bowl offers added room and comfort.
- Skirted trapway simplifies cleaning.
- 2" (51 mm) fully-glazed trapway.
- Combines with the 402098 or 402098-RA tank to create a complete 402095 or 402095-RA Brella two-piece toilet.

Material

- Vitreous china.

Installation


- Standard 12" (305 mm) rough-in.
- Patented ReadyLock™ installation system is a simple solution for skirted toilets that saves time, hassle and eliminates the need to drill into the floor for a standard 12" (305 mm) rough-in.
- Seat and supply line sold separately.
- Three-bolt tank-to-bowl installation.

Recommended Products/Accessories

K-4008 Reveal® Quiet-Close™ Elongated Toilet Seat
402098 Toilet tank
402098-RA
K-23726 Drain treatment

Included Components

Additional Components:
ReadyLock™ installation system



Codes/Standards

ASME A112.19.2/CSA B45.1

STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

■	0	White
---	---	-------



Brella™ Comfort Height®

Elongated toilet bowl

402101

No image available.

This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Two-piece, Floor-mount
Waste Outlet:	Floor
Flush type:	Gravity siphon washdown
Trap passageway:	2" (51 mm)
Water Consumption	
Full:	1.28 gpf (4.8 lpf)
Water surface size:	5-1/16" x 4-9/16" (129 mm x 115 mm)
Rim to water surface:	8-9/16" (217 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.