

Features

- Elongated bowl offers added room and comfort
- Skirted trapway simplifies cleaning
- 2" (51 mm) glazed trapway
- Combines with the 402098 or 402098-RA tank to create a complete 402095 or 402095-RA Brella two-piece toilet
- Patented ReadyLock® installation system, a simple solution for skirted toilets, saves time, hassle, and eliminates the need to drill into the floor for standard 12" (305 mm) rough-in

Installation

- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately
- Three-bolt quick-connect installation

Recommended Products/Accessories

402098 Toilet tank
402098-RA 1.28 gpf toilet tank
K-23726 Drain treatment
K-26801 Impro® ReadyLatch® Quiet-Close™ elongated toilet seat



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification

STERLING® Toilet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------

No image available.

This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Gravity siphon washdown
Trap passageway:	2" (51 mm)
Water surface size:	5-1/16" x 4-9/16" (129 mm x 115 mm)
Rim to water surface:	8-9/16" (217 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.