



Valton™

Two-piece round-front toilet 402314

Features

- Two-piece toilet.
- Round-front bowl offers an ideal solution for smaller baths and powder rooms.
- 1.6 gallons per flush (gpf).
- Color-matched left-hand white trip lever included.
- 2" (51 mm) fully-glazed trapway.
- Combination consists of the 403377 bowl and 404562 tank.

Technology

- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models.

Installation

- Standard 12" (305 mm) rough-in.
- Three-bolt installation.
- Seat and supply line sold separately.

Recommended Products/Accessories

K-20111 Brevia™ Quiet-Close™ Round-Front Toilet Seat
K-4639 Cachet® Quiet-Close™ Round-Front Toilet Seat
K-5420 Low-Profile Bolt Caps
K-23726 Drain treatment

Included Components

Product consists of:

403377 Round-front toilet bowl
404562 Toilet tank



Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992

STERLING® Warranty - Toilets and Lavatories


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
--	---	-------



Technical Information

All product dimensions are nominal.
 Toilet type: Two-piece, Floor-mount
 Waste Outlet: Floor
 Bowl shape: Round-front
 Flush type: Gravity siphon jet
 Water Consumption
 Full: 1.6 gpf (6 lpf)
 Rough-in: 12" (305 mm)

Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)
 Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.
 For back-to-back toilet installations: Use only a 45° double wye fitting.