

### Features

- Two-piece design.
- Round-front bowl offers an ideal solution for smaller baths and powder rooms.
- 1.6 gpf (6.0 lpf)
- Color-matched left-hand white trip lever included.
- 2" (51 mm) fully-glazed trapway.
- Combination consists of the 403377 bowl and 404562 tank.

### Technology

- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models.

### Installation

- Standard 12" (305 mm) rough-in.
- Three-bolt quick-connect installation.
- Seat and supply line sold separately.

### Recommended Products/Accessories

- K-20111 Brevia™ Quiet-Close™ Round-Front Toilet Seat
- K-4639 Cachet® Quiet-Close™ Round-Front Toilet Seat
- K-5420 Low-Profile Bolt Caps
- K-23726 Drain treatment
- K-23724 Toilet cleaner & disinfectant
- K-23734 Toilet bowl cleaner & disinfectant

### Included Components

Product consists of:

- 403377 Round-front toilet bowl
- 404562 Toilet tank



### Codes/Standards

ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992


### STERLING® Warranty - Toilets and Lavatories


See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
--	---	-------



**Technical Information**

All product dimensions are nominal.

Toilet type: Two-piece, Floor-mount  
Waste Outlet: Floor  
Bowl shape: Round-front  
Flush type: Gravity siphon jet

Water Consumption  
Full: 1.6 gpf (6 lpf)  
Rough-in: 12" (305 mm)

**Fixture Supply Requirements**

Min static pressure: 15 psi (103.4 kPa)  
Max static pressure: 80 psi (551.6 kPa)

**Notes**

Install this product according to the installation instructions.  
For back-to-back toilet installations: Use only a 45° double wye fitting.