

### Features

- Two-piece design
- Round-front bowl offers an ideal solution for smaller bathrooms and powder rooms
- Top-mount dual-flush actuator offers a choice of 1.0 or 1.28 gpf (3.8 or 4.8 lpf)
- 2" (51 mm) fully glazed trapway
- Combination consists of the 403377 bowl and 404553 tank

### Technology

- Dual-flush technology allows you to choose between a full or partial flush
- Pro Force™ Plus flushing technology delivers greater flushing power than previous Pro Force™ models

### Installation

- Standard 12" (305 mm) rough-in
- Three-bolt quick-connect installation
- Seat and supply line sold separately

### Recommended Products/Accessories

- K-20111 Brevia™ Quiet-Close™ round-front toilet seat
- K-5589 Purefresh™ Deodorizing round-front toilet seat
- K-5420 Low-Profile Bolt Caps
- K-23726 Drain treatment
- K-186 Dual Flush Actuator

### Included Components

- 403377 Round-front toilet bowl
- 404553 Toilet tank



### Codes/Standards

- ASME A112.19.2/CSA B45.1
- ASME A112.19.14
- DOE - Energy Policy Act 1992
- EPA WaterSense™
- California Energy Commission (CEC)

### STERLING® Toilet Limited Warranty


See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



**Technical Information**

All product dimensions are nominal.

Toilet type: Floor-mount  
Waste Outlet: Floor  
Bowl shape: Round-front  
Trap passageway: 2" (51 mm)  
Rim to water surface: 5" (127 mm)  
Rough-in: 12" (305 mm)

**Notes**

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.