



# Windham™

## Round-front toilet bowl

### 402323-RA

#### Features

- Two-piece toilet.
- Round-front bowl offers an ideal solution for smaller baths and powder rooms.
- Standard height.
- 1.6 gallons per flush (gpf).
- Includes Polished Chrome right-hand trip lever.
- 2-1/8" (54 mm) fully-glazed trapway.
- Combination consists of 403017 bowl and 402363-RA tank.

#### Technology

- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models.

#### Installation

- Three-bolt quick-connect installation.
- Standard 12" (305 mm) rough-in.
- Seat and supply line sold separately.

#### Recommended Products/Accessories

K-20111 Brevia™ Quiet-Close™ Round-Front Toilet Seat  
K-4639 Cachet® Quiet-Close™ Round-Front Toilet Seat  
K-9466-R Right-Hand Trip Lever  
K-5420 Low-Profile Bolt Caps  
K-23726 Drain treatment

#### Included Components

Product consists of:

403017 Round-front toilet bowl  
402363-RA Toilet tank

Additional Components:

Tank cover, Trip lever, Tank mounting hardware, Bolt cap accessory pack.



#### Codes/Standards



ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992


#### STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	KOHLER Biscuit



**Technical Information**

All product dimensions are nominal.

- Toilet type: Two-piece, Floor-mount
- Waste Outlet: Floor
- Bowl shape: Round-front
- Flush type: Flush Valve
- Trap passageway: 2-1/8" (54 mm)
- Water Consumption
  - Full: 1.6 gpf (6 lpf)
- Water surface size: 10" x 8" (254 mm x 203 mm)
- Rim to water surface: 6-3/16" (157 mm)
- Rough-in: 12" (305 mm)

**Notes**

Install this product according to the installation instructions.  
For back-to-back toilet installations: Use only a 45° double wye fitting.