



# Windham™

Elongated toilet bowl  
**402324-RA**

## Features

- Two-piece toilet.
- Elongated bowl offers added room and comfort.
- Standard height.
- 1.6 gallons per flush (gpf).
- Includes Polished Chrome right-hand trip lever.
- 2-1/8" (54 mm) fully-glazed trapway.
- Combination consists of 403217 bowl and 402363-RA tank.

## Technology

- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models.

## Installation

- Three-bolt quick-connect installation.
- Standard 12" (305 mm) rough-in.
- Seat and supply line sold separately.

## Recommended Products/Accessories

K-20110 Brevia™ Quiet-Close™ Elongated Toilet Seat  
K-4636 Cachet® Quiet-Close™ Elongated Toilet Seat  
K-9466-R Right-Hand Trip Lever  
K-5420 Low-Profile Bolt Caps  
K-23726 Drain treatment

## Included Components

Product consists of:

403217 Elongated toilet bowl  
402363-RA Toilet tank

Additional Components:

Bolt cap accessory pack  
Tank cover  
Tank mounting hardware  
Trip lever



## Codes/Standards



ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992


## STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	KOHLER Biscuit



### Technical Information

All product dimensions are nominal.

Toilet type:	Two-piece, Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Gravity siphon jet
Trap passageway:	2-1/8" (54 mm)
Water Consumption	
Full:	1.6 gpf (6 lpf)
Rough-in:	12" (305 mm)

### Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.