

### Features

- 1.28 gpf (4.8 lpf)
- Left-hand Polished Chrome trip lever
- Combines with 403017, 403217, 403317 toilet bowl to make a complete 402320, 402321, 402322 toilet
- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models

### Installation

- Three-bolt quick-connect installation
- Standard 12" (305 mm) rough-in
- Supply line sold separately



### Codes/Standards

ASME A112.19.2/CSA B45.1  
IAPMO Certification


### STERLING® Toilet Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



**Windham™**  
Toilet tank  
**402362**

No image available.  
This product is a component and not intended to be a standalone installation.

### **Technical Information**

All product dimensions are nominal.

Toilet type: Bowl-mount  
Rough-in: 12" (305 mm)

### **Notes**

Install this product according to the installation instructions.