



Windham™

Round-front toilet bowl
403017

Features

- Round-front bowl offers an ideal solution for smaller bathrooms and powder rooms
- Standard height
- 2-1/8" (54 mm) fully glazed trapway
- Combines with 402362, 402362-RA, 402363, 402363-RA tanks to make a complete 402320, 402320-RA, 402323, 402323-RA toilet
- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models

Installation

- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately

Recommended Products/Accessories

- 402362 Toilet tank
- 402362-RA Toilet tank
- 402363 Toilet tank
- 402363-RA Toilet tank
- K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification


STERLING® Toilet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Windham™
Round-front toilet bowl
403017

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Round-front
Flush type:	Gravity siphon jet
Trap passageway:	2-1/8" (54 mm)
Water surface size:	10" x 8" (254 mm x 203 mm)
Rim to water surface:	6" (152 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.