



# Windham™

Elongated toilet bowl  
404210

## Features

- Elongated bowl only; pairs with Windham toilet tank
- Uses 1.6 gallons of water per flush
- 2" (51 mm) fully glazed trapway

## Installation

- 10" (254 mm) rough-in

## Recommended Products/Accessories

K-23726 Drain treatment



## Codes/Standards

ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992  
IAPMO Certification


## STERLING® Toilet Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|

|   |   |       |
|---|---|-------|
|  | 0 | White |
|---|---|-------|



**Windham™**  
Elongated toilet bowl  
**404210**

No image available.  
This product is a component and not intended to be a standalone installation.

**Technical Information**

All product dimensions are nominal.

Toilet type: Floor-mount  
Bowl shape: Elongated  
Trap passageway: 2" (51 mm)  
Rough-in: 10" (254 mm)

**Notes**

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.