



Riverton™

Toilet tank with Insuliner® tank liner
404552

Features

- Tank only; pairs with Windham toilet bowl
- 1.28 gpf (4.8 lpf)
- Pro Force® flushing technology
- Includes an insulating tank liner

Installation

- Standard 12" (305 mm) rough-in
- Three-bolt quick-connect installation



Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
IAPMO Certification

STERLING® Toilet Limited Warranty

See website for detailed warranty information.



Riverton™
Toilet tank with Insuliner® tank liner
404552

No image available.

This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount
Rough-in: 12" (305 mm)

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.