



Southampton®

Pedestal Bathroom Sink Basin
446424

Features

- Wall-mount or for use with pedestal 448420.
- Grade A vitreous china with a hard, glossy finish.
- 4 centerset faucet holes.
- Center drain and overflow.

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23725 Cast iron cleaner



Codes/Standards



ASME A112.19.2/CSA B45.1

STERLING® Warranty - Toilets and Lavatories

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	KOHLER Biscuit



Southampton®
Pedestal Bathroom Sink Basin
446424

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Bowl configuration: Single
Installation: Pedestal
Bowl area (Only): Length: 20-7/8" (530 mm)
Width: 12-1/4" (311 mm)
Water depth: 4" (102 mm)
Number of deck holes: 3
Faucet hole spacing: 4" (102 mm)
Drain hole: 1-1/4" (32 mm)

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.