



Standard Framed Sliding Bath Door 500C-59

Features

- Framed
- 1/8" glass
- Out-of-plumb adjustability
- Tempered glass ensures maximum safety and durability
- Anodized aluminum prevents rusting and corrosion

Installation

- Not for use in hospitality.
- For residential use only.

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
-------	------	-------------

	S	
--	---	--

Available Glass Options

Code	Description
------	-------------

	Clear
--	-------



Technical Information

All product dimensions are nominal.
 Installation type: For bath installation
 Opening Width - Min: $54"$ (1372 mm)
 Opening Width - Max: $59"$ (1499 mm)
 Walk-through - Min: $24\text{-}7/16"$ (621 mm)
 Walk-through - Max: $29\text{-}7/16"$ (748 mm)
 Glass thickness: $1/8"$ (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of $58"$ (1473 mm) to allow for installation clearance.