



Standard Framed sliding bath door 500C-59

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Tempered glass ensures maximum safety and durability.

Material

- Anodized aluminum prevents rust and corrosion.

Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

DISCONTINUED

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Glass Options

Code	Description
	Clear

DISCONTINUED


This product has been discontinued.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

12-29-2021 10:08 - US//CA



Technical Information

All product dimensions are nominal.

Installation type: For bath installation

Opening Width - Min: 54" (1372 mm)

Opening Width - Max: 59" (1499 mm)

Walk-through - Min: 24-7/16" (621 mm)

Walk-through - Max: 29-7/16" (748 mm)

Base-To-Wall Radius - Max: 1/4" (6 mm)

Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 58" (1473 mm) to allow for installation clearance.