



Standard

Framed sliding bath door

500C-59

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
-------	------	-------------

	S	Silver
--	---	--------

Available Glass Options

Code	Description
------	-------------

	Clear
--	-------



Technical Information

All product dimensions are nominal.

Installation type: For bath installation

Opening Width - Min: 54" (1372 mm)

Opening Width - Max: 59" (1499 mm)

Walk-through - Min: 24-7/16" (621 mm)

Walk-through - Max: 29-7/16" (748 mm)

Base-To-Wall Radius 1/4" (6 mm)

– Max:

Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 58" (1473 mm) to allow for installation clearance.