



McAllister®

Under-Mount Kitchen Sink

50200

Features

- 9-3/4"-deep single bowl.
- 3-3/4" rear drain opening.
- Stainless steel with luster finish.
- SilentShield® sound-absorption technology offers quieter performance.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- 7400 Sink Strainer

Included Components

- Additional Components:
- Installation hardware





Codes/Standards


ASME A112.19.3/CSA B45.4

Lifetime Limited Warranty for KOHLER® Stainless Steel Sinks

See website for detailed warranty information.



* Allow clearance around sink rim for clip attachment.



Technical Information

All product dimensions are nominal.

Installation:	Under-mount
Bowl area (Only):	Length: 22" (559 mm) Width: 19" (483 mm) Bowl depth: 9-1/2" (241 mm) Water depth: 9-1/2" (241 mm)
Drain hole:	3-3/4" (94 mm)
Template:	1315845-7, required, included

Notes

Install this product according to the installation instructions.