



McAllister®

23-3/4" undermount single-bowl kitchen sink

50200

Features

- No faucet holes; requires wall- or counter-mount faucet
- 9-3/4" depth provides generous workspace
- 3-3/4" (95 mm) drain opening
- Stainless steel with luster finish

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner

Optional Products/Accessories

7400 Stainless Steel Sink Drain and Strainer



Codes/Standards

ASME A112.19.3/CSA B45.4

IAPMO Certification

STERLING® Stainless Steel Sinks

Lifetime Limited Warranty


See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

2-14-2024 20:41 - US



Technical Information

All product dimensions are nominal.

Bowl area (Only): Length: 22" (559 mm)
 Width: 19" (483 mm)
 Bowl depth: 9-1/2" (241 mm)
 Water depth: 9-1/2" (241 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1315845-7, required, included

Notes

Install this product according to the installation instructions.