



Finesse™ Quick Install™

Frameless Sliding Bath Door

5325EZ-57

Features

- Frameless
- 1/4" glass
- CleanCoat technology
- Quick Install system
- Interior and exterior towel bars
- Out-of-plumb adjustability
- Tempered glass ensures maximum safety and durability
- Anodized aluminum prevents rusting or corrosion

Installation

- Not for use in hospitality.
- For residential use only.

Included Components

Additional Components:

- Hardware kit
- hex wrench



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

DR

N

S

Available Glass Options

Code	Description
------	-------------

Clear


Lake Mist™

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

4-25-2019 22:45 - US/CA



Technical Information

All product dimensions are nominal.

Installation type: For bath installation

Opening Width - Min: 56" (1422 mm)

Opening Width - Max: 57-1/2" (1461 mm)

Walk-through - Min: 24-15/16" (633 mm)

Walk-through - Max: 26-7/16" (672 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 57-3/4" (1467 mm) to allow for installation clearance.