



Finesse™ Quick Install™

Frameless sliding shower door
5375EZ-45

Technology

- Frameless
- 1/4" glass
- CleanCoat® nanotechnology helps prevent bacteria, mildew and water stains on your glass, making it easy to clean and looking new.
- Quick Install system
- Interior and exterior towel bars
- Out-of-plumb adjustability
- Tempered glass ensures maximum safety and durability
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Included Components

Additional Components:

- Hardware kit
- hex wrench



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors


See website for detailed warranty information.

Available Glass Options

Code	Description
------	-------------

Clear

Lake Mist™



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 44" (1118 mm)

Opening Width - Max: 45-1/2" (1156 mm)

Walk-through - Min: 18-15/16" (481 mm)

Walk-through - Max: 20-7/16" (519 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 72-5/16" (1837 mm) to allow for installation clearance.